

ข้อมูลด้านเทคนิค

Fluke H900 Test Lead Holder



คุณลักษณะสำคัญ

- Heavy duty construction with mounting holes
- Holder has 10 slots for wires up to 8 mm in diameter
- Over-all dimensions: 27.9 cm L x 8.9 cm W x 3.2 cm H
- One year warranty

ภาพรวมผลิตภัณฑ์: Fluke H900 Test Lead Holder

- Heavy duty construction with mounting holes
- Holder has 10 slots for wires up to 8 mm in diameter
- Over-all dimensions: 27.9 cm L x 8.9 cm W x 3.2 cm H
- One year warranty

รุ่น



Fluke H900

Test Lead Holder

Fluke. ให้โลกของคุณ คงอยู่แต่ละก้าวต่อไป

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa
+31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com/th-th

©2021 Fluke Corporation. Specifications subject to
change without notice.
12/2021

Modification of this document is not permitted without
written permission from Fluke Corporation.