


Fluke STL120-III Shielded Test Leads Set



คุณลักษณะสำคัญ

- Bandwidth: 12,5 MHz
- Maximum Signal Voltage: 600V rms. CAT III per IEC 61010-031:2008
- Maximum Voltage to Ground: 600V rms. CAT III per IEC 61010-031:2008
- Maximum Current: 1A
- 2mm add-on testpin: 600V CAT II per IEC 61010-031:2008
- Length: 1.2m (48)

ภาพรวมผลิตภัณฑ์: Fluke STL120-III Shielded Test Leads Set

Set of two (one red, one gray) double insulated silicone shielded test leads for noise free measurements. Specially designed for use with the Fluke ScopeMeter 120 Series. Compatible with AC120 Alligator Clips and HC120 Hook Clips. Safety designed ground leads included. Integral strain relieve and extra hard probe tips provide extra long service life. features safety designed shrouded plugs and notched tip to prevent probe from sliding.

ข้อมูลจำเพาะ: Fluke STL120-III Shielded Test Leads Set

Specifications	
Bandwidth	12,5 MHz
Maximum signal voltage	600 V rms CAT III per IEC 61010-031:2008

Maximum voltage to ground	600 V rms CAT III per IEC 61010-031:2008
Maximum vcurrent	1 A
2 mm add-on testpin	600 V CAT II per IEC 61010-031:2008
Length	1.2 m (48)

รุ่น



Fluke STL120 III

Shielded Test Leads Set

Fluke. ให้โลกของคุณ คงอยู่แต่ละก้าวต่อไป

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa
+31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com/th-th

©2021 Fluke Corporation. Specifications subject to
change without notice.
12/2021

Modification of this document is not permitted without
written permission from Fluke Corporation.