

ข้อมูลด้านเทคนิค

Fluke TL76 2mm/4mm Test Lead Set



คุณลักษณะสำคัญ

- Removable, insulated IC caps allow probing on closely spaced leads and compliance with GS38
- CAT II 1000 V, 10 A rating
- CAT III 1000 V, CAT IV 600V only with protective cap
- One year warranty

ภาพรวมผลิตภัณฑ์: Fluke TL76 2mm/4mm Test Lead Set

One pair (red, black) silicone test leads with right angle shrouded 4 mm (0.16 in) banana plugs.

รุ่น



Fluke TL76

- One pair (red, black) 1.5 meter long silicone test leads with right angle shrouded banana plug
- Lantern tip (removable) for use with European wall sockets (4 mm Ø)
- Lantern tip can be removed for easy access to terminal blocks (2 mm Ø)

Fluke. ให้โลกของคุณ คงอยู่แต่ละก้าวต่อไป

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa
+31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com/th-th

©2021 Fluke Corporation. Specifications subject to
change without notice.
12/2021

Modification of this document is not permitted without
written permission from Fluke Corporation.