

ข้อมูลด้านเทคนิค

Fluke TL82 Automotive Pin and Socket Adapter Set



ภาพรวมผลิตภัณฑ์: Fluke TL82 Automotive Pin and Socket Adapter Set

An absolute must-have for work on Asian or European vehicles. This collection of male and female adapters allows you to make firm connection to pin and socket connectors. Useful when making voltage, frequency, duty cycle or resistance measurements and a must when measuring current requiring the meter be placed in series in the circuit.

รุ่น



Fluke TL82

Fluke TL82 Automotive Pin & Socket Adapter Set
Automotive Pin & Socket Adapter Set

Set contains:

- Retractable shrouded test leads complete set of 8 pin-and-socket adapters with flexible tips; one red and one black in the following sizes:
 - Size 22 contact 0.030 in. (0.76 mm) rated 3 A
 - Size 20 contact 0.040 in. (1.02 mm) rated 3 A
 - Size 16 contact 0.063 in. (1.60 mm) rated 3 A
 - Size 12 contact 0.093 in. (2.36 mm) rated 3 A
- Tested to 60 V DC

Fluke. ทั่วโลกของคุณ คงอยู่แค่ก้าวต่อไป

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa
+31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com/th-th

©2021 Fluke Corporation. Specifications subject to
change without notice.
11/2021

Modification of this document is not permitted without
written permission from Fluke Corporation.