

ข้อมูลด้านเทคนิค

## VPS220-R – Voltage Probe Set, 100:1, one red



### ภาพรวมผลิตภัณฑ์: VPS220-R – Voltage Probe Set, 100:1, one red

Double insulated voltage probe for ScopeMeter 190 series.

Each probe set includes:

- 600 V CAT III / 1000 V CAT II rated 100:1 Voltage Probe
- Hook Clip for Probe Tip
- Ground Lead with Mini Alligator
- Insulation Sleeve
- 30 V CAT II rated Ground Spring for Probe Tip


Specification:

- Attenuation: 100:1
- Bandwidth: 200 MHz
- Max. Input Voltage 1000 V CAT II or 600 V CAT III
- Max. Voltage to ground: 1000 V CAT II or 600 V CAT III per IEC / EN61010-031
- Input Resistance: 100 M $\Omega$
- Input Capacitance: 4.6 pF
- Compensation range: 10 to 25 pF
- Cable Length: 1.2 m

## ข้อมูลจำเพาะ: VPS220-R – Voltage Probe Set, 100:1, one red

Specification	
Attenuation	100:1
Bandwidth	200 MHz
Max. input voltage	1000 V CAT II or 600 V CAT III
Max. voltage to ground	1000 V CAT II or 600 V CAT III per IEC / EN61010-031
Input resistance	100 M $\Omega$
Input capacitance	4.6 pF
Compensation range	10 to 25 pF
Cable length	1.2 m

**รูป**



**Fluke VPS220-R**

Voltage Probe Set, 100:1, One Red

Each probe set includes:

- 600 V CAT III / 1000 V CAT II rated 100:1 voltage probe
- Hook clip for probe tip
- Ground lead with mini alligator
- Insulation sleeve
- 30 V CAT II rated ground spring for probe tip

**Fluke. ให้โลกของคุณ คงอยู่แต่ละก้าวต่อไป**

Fluke Corporation  
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:  
In the U.S.A. (800) 443-5853  
In Europe/M-East/Africa  
+31 (0)40 267 5100  
In Canada (800)-36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com/th-th](http://www.fluke.com/th-th)

©2021 Fluke Corporation. Specifications subject to  
change without notice.  
11/2021

Modification of this document is not permitted without  
written permission from Fluke Corporation.