

ข้อมูลด้านเทคนิค

Fluke HC120 Hook Clips (Set of 2: Red, Gray)



ภาพรวมผลิตภัณฑ์: Fluke HC120 Hook Clips (Set of 2: Red, Gray)

Set of two (one red, one gray) Hook Clips, designed for use with STL 120 Shielded Test Leads, VPS40 and TL75 Test Leads. Accepts wires up to 2.5 mm. The contact material is made of reinforced nickel plated steel

ข้อมูลจำเพาะ: Fluke HC120 Hook Clips (Set of 2: Red, Gray)

General Specifications	
Maximum voltage	600 V rms. CAT III per IEC 1010-2-031
Maximum wire size	2.5 mm
Contact material	Nickel plated steel

รุ่น



Fluke HC120

Fluke. ทั่วโลกของคุณ คงอยู่แค่ก้าวต่อไป

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa
+31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com/th-th

©2021 Fluke Corporation. Specifications subject to
change without notice.
11/2021

Modification of this document is not permitted without
written permission from Fluke Corporation.