

ข้อมูลด้านเทคนิค

Fluke TP82 Insulation Piercing Clip Set



คุณลักษณะสำคัญ

- Banana jack accepts all DMM and banana jack leads
- Non-rotating banana jack prevents leads from tangling, allowing you to tighten/loosen clamp while still connected to the test lead
- For use with test leads with 2 mm probes
- Tested to 60 V DC

ภาพรวมผลิตภัณฑ์: Fluke TP82 Insulation Piercing Clip Set

Stainless steel probe pierces insulation on 14, 16 and 18 gauge wire. You control needle depth to minimize insulation damage. Essential for use under hood or under dash. Use it on fuel injectors or sensors while providing complete insulation to grounding due to design.

รุ่น**Fluke TP82**Fluke TP82 Insulation Piercing Clip Set

Fluke. ทั่วโลกของคุณ คงอยู่แค่ก้าวต่อไป

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa
+31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com/th-th

©2021 Fluke Corporation. Specifications subject to
change without notice.
11/2021

Modification of this document is not permitted without
written permission from Fluke Corporation.