

ข้อมูลด้านเทคนิค

เลนส์อินฟราเรดแบบมุมกว้าง



ภาพรวมผลิตภัณฑ์: เลนส์อินฟราเรดแบบมุมกว้าง

มีขอบเขตการมองเห็นกว้างเพื่อการตรวจสอบวัตถุขนาดใหญ่ – ใช้งานได้กับรุ่น TiX1000, TiX660 และ TiX640

การใช้งาน: ผนังหรือด้านข้างอาคาร หรือต้องทำงานในพื้นที่แคบ

ข้อมูลจำเพาะ: เลนส์อินฟราเรดแบบมุมกว้าง

ลักษณะทั่วไป	
คำอธิบายเกี่ยวกับเลนส์	เลนส์มุมกว้าง
ระยะโฟกัส	15 มม.
โฟกัส	0.47 ม.
1024 x 768	
iFOV	1.1 mRad
FOV	68.7 x 50.7°
640 x 480	
iFOV	1.7 mRad
FOV	62.3 x 46.4°

รุ่น

**FLK-Xlens/Wide**

Applications: Entire wall or side of building or the need to work in tight spaces.
Compatible with TiX1000, TiX660 and TiX640 infrared cameras.

Fluke. ให้โลกของคุณ คงอยู่แค่ก้าวต่อไป

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa
+31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com/th-th

©2021 Fluke Corporation. Specifications subject to
change without notice.
12/2021

Modification of this document is not permitted without
written permission from Fluke Corporation.