

ข้อมูลด้านเทคนิค

Fluke 700PCK Pressure Calibration Kit



ภาพรวมผลิตภัณฑ์: Fluke 700PCK Pressure Calibration Kit

Description: The Fluke 700PCK makes it possible to calibrate your pressure modules at your facility using your own precision pressure standards.

Application: When installed on your PC, the WindowsT-based software easily steps you through an as-found verification, a calibration adjustment, and an as-left verification. Calibration data is captured for import to your database. A 386 or better PC running Windows 3.1 or better is required, along with a precision pressure standard with an uncertainty of less than 1/4 that of the pressure module being verified.

Included: The kit consists of a power supply, an interface adapter, appropriate cables, and Fluke 700PC Pressure Module Calibration Software.

Warranty: One year

รุ่น

**Fluke 700PCK**

Pressure Calibration Kit

Included: The kit consists of a power supply, an interface adapter, appropriate cables, and Fluke 700PC Pressure Module Calibration Software.

Warranty: One year

Fluke. ให้โลกของคุณ คงอยู่แต่ละก้าวต่อไป

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa
+31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com/th-th

©2021 Fluke Corporation. Specifications subject to
change without notice.
12/2021

Modification of this document is not permitted without
written permission from Fluke Corporation.