

ข้อมูลด้านเทคนิค

ชุดเครื่องมือทดสอบไฟฟ้าพร้อมด้วยกรอบหุ้มและ IAC II



คุณลักษณะสำคัญ

- T5-1000 electrical tester automatically measures volts AC and volts DC with precise digital resolution
- Includes easy, accurate OpenJaw™ current measurement
- Displays resistance to 1000 Ω
- Includes a continuity beeper for quick go/no-go tests
- All inputs are protected to EN61010-1 CAT III 1000 V CAT IV 600 V. UL, CSA
- 1AC II offers Voltbeat™ technology and continuous self-test so you always know it's working
- Upon detection of voltage, the VoltAlert™ tip glows and beeper sounds
- CAT IV 1000 V for added protection

ภาพรวมผลิตภัณฑ์: ชุดเครื่องมือทดสอบไฟฟ้าพร้อมด้วยกรอบหุ้มและ IAC II

ชุดเครื่องมือทดสอบกระแสไฟฟ้า ความต่อเนื่อง และกระแสไฟฟ้าพร้อมด้วยกรอบหุ้ม ไม่มีค่าใช้จ่ายสำหรับ 1AC

รุ่น



Fluke T5-H5-1AC II Kit

ชุดนี้ประกอบด้วย:

- Fluke T5-1000
- Fluke 1AC II
- H5

Fluke. ทั่วโลกของคุณ คงอยู่แค่ก้าวต่อไป

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa
+31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com/th-th

©2022 Fluke Corporation. Specifications subject to
change without notice.
01/2022

Modification of this document is not permitted without
written permission from Fluke Corporation.