

ข้อมูลด้านเทคนิค

Fluke ScopeMeter 190-204/S Portable Digital Oscilloscope



คุณลักษณะสำคัญ

See More, Fix More with the Four-Channel CAT IV Rated Fluke ScopeMeter® 190-204/S

The Fluke ScopeMeter 190-204/S combine the highest safety ratings and rugged portability with the high performance of a bench oscilloscope. Designed for plant maintenance engineers and technicians, these tough ScopeMeter test tools go into harsh, dirty, and hazardous industrial conditions to test everything from micro-electronics to power electronics applications.

The ScopeMeter 190-204/S is the one test tool you will reach for to tackle just about any troubleshooting task. They include a multimeter, TrendPlot™ and ScopeRecord™ roll paperless recorder modes and hands free operation with Connect-and-View™ triggering, and much more:

- Four electrically isolated inputs
- CAT III 1000 V / CAT IV 600 V safety rated
- 200 MHz bandwidth model
- 2.5 GS/s
- Deep memory: 10,000 samples per channel waveform capture so you can zoom in on the details
- Quad meter measurements via scope BNC inputs
- Connect-and-View continuous auto-trigger, single shot, pulse width, and video triggering
- ScopeRecord roll mode, capture waveform sample data for up to 48 hours
- TrendPlot, trend measurement readings for up to 22 days
- Advanced automatic measurements, power (Vpwm, VA, W, PF) and time (mAs, V/s, w/s)

- IP-51 rated for dust and drip proof to withstand harsh environments
- Isolated USB ports for memory devices and PC connectivity
- Li-Ion battery for extended operating timespan: up to 7 hours (BP291 included standard)
- Charge spare battery using optional external battery charger (EBC290)
- Easy-access battery door to make it easy to swap batteries
- A handy slot to tether and lock down the oscilloscope while unattended using a standard Kensington® lock

ภาพรวมผลิตภัณฑ์: Fluke ScopeMeter 190-204/S Portable Digital Oscilloscope

Fluke 190-204/S – 20 years of ScopeMeter® Test Tool Innovation

As the first four-channel portable scope safety rated CAT III 1000V / CAT IV 600V, the Fluke ScopeMeter 190-204/S combines an unprecedented level of performance, ruggedness, and portability with 200 MHz bandwidth and real-time sampling rates up to 2.5 GS/s and 200 ps resolution to capture noise and other disturbances. This model features deep memory up to 10,000 samples per channel; so you can examine very small parts of the waveform in detail, and it is IP-51 rated to withstand dust, drips, humidity, and wide temperature variations. Fluke ScopeMeter test tools are hand-held battery operated, designed to meet the demands of field service professionals.

Gain Four Times the Diagnostic Power Plus CAT IV Safety Rating

The Fluke ScopeMeter 190-204/S portable scope is double-insulated four-channel floating oscilloscopes safety rated for measurements in CAT III 1000V/CAT IV 600V environments.

Three-dimensional testing for industrial systems

Inspect input signals, output feedback loops or safety interlocks simultaneously to find a range of problems including:

- Circuit voltage/current overloading
- Signal timing measurements and synchronization issues
- Attenuation/input impedance mismatch
- Signal fluctuation/drift

Three-phase testing for diagnosing VSD, power inverters, and converters

- Test for harmonics, transients and loads at the three-phase power input
- Troubleshoot DC to AC converters for faulty IGBT gates or filter circuits
- Test PWM output for reflections and transients or voltage unbalance

Safely measure from mV to kV

Standard probes that cover a wide application range from mV to kV prepare you for anything from micro-electronics to heavy duty medium voltage electrical applications. Independent isolated inputs eliminate the risk of accidental ground short circuits by allowing you to make measurements in mixed circuits with separate ground references.

Take on the harshest conditions with the only IP-51-rated Scope on the Market

Rugged and shock-proof, all ScopeMeter portable oscilloscopes are built for harsh environments. Their sealed cases protect them from dust, water vapor, drips, humidity and airborne pollutants ensuring reliable accurate performance every time you need them.

Built in multimeter to quickly and conveniently perform precise measurements

Built-in digital multimeter Fluke 190-204/S 4-channel models incorporate quad meter measurements via the 4-channel scope BNC inputs. Conveniently switch from waveform analysis to precise multimeter measurements using the built in 5000 count digital multimeter. Measurement functions include VDC, VAC, VAC + DC, resistance, continuity and diode test. Measure



current and temperature using suitable shunt, probe or adapter with wide range of scaling factors.

Work a Full Shift on a Single Charge

New high-performance batteries take advantage of Li-ion technology to keep you going strong for up to seven hours. And with the easy-access battery door you can make battery swaps fast.

Capture and Share Waveforms Easily with New USB connectivity

Two USB ports, electrically isolated from measurement input circuits offer you easy USB connectivity to a PC or USB memory devices. Store unlimited waveform, screen captures or instrument steps to a USB memory device. Connect to a PC USB interface to transfer and archive critical measurement data using FlukeView software for windows.

See a Stable Display Instantly with Connect-and-View™ Triggering

Connect-and-View™ automatically sets up correct triggering by recognizing signal patterns. Without touching a button, you get a stable, reliable, and repeatable display of virtually any signal including motor drive and control signals. Expedites measuring several test-points in rapid succession.

Record Up to 48 Hours of High-Resolution Waveforms with ScopeRecord™

ScopeRecord memory stores up to 30,000 data points per channel, capturing intermittents and fast glitches. (Two sets of multiple-channel recordings can be stored for later analysis.)

- Stores events like motion profiles, UPS, power supply, and motor start-ups
- With the Stop-on-Trigger mode, the ScopeMeter 190-204/S automatically recognizes a power failure and stores the waveform data preceding it
- With the waveform zoom (up to 100x) you can look at the smallest details, like individual power cycles

Record up to 22 days with TrendPlot™ paperless recorder to find intermittent faults

Intermittent faults can be caused by bad connections, dust, dirt, corrosion, or simply broken wiring or connectors. Line outages, sags, or starting and stopping a motor can also cause a machine to stop. The TrendPlot function in the Fluke ScopeMeter test tool helps find those faults by:

- Plotting minimum and maximum peak values and average over time up to 22 days
- Plotting any combination of voltages, amps, temperature, frequency and phase for all four inputs, all with time and date stamp to pinpoint faults

Tektronix THS3000 Handheld Oscilloscope

The Tektronix THS3000 Handheld Oscilloscope has been discontinued, but customers can find a nearly identical replacement with the Fluke 190 ScopeMeter® Test Tool.

See how the models compare:

	THS3000	Fluke 190 ScopeMeter Feature / Capability Differences	
Platform	The Tektronix THS 3000 and Fluke 190 ScopeMeter Test Tool share the same electronics, with some feature differences highlighted below		
Sampling size	2.5 GS/s max real time sampling rate; 5 GS/s max sequential sampling rate	2.5 GS/s max real time sampling rate	Real time sampling rate to capture all the details for troubleshooting electronic circuits
Safety rating	CAT III	CAT IV	Fluke 190 Series II covers all application installations from CAT II to CATIV
IP rating according to IEC529	IP 41	IP 51	Fluke 190 Series with IP51 rating is less susceptible to harm caused by environmental conditions no matter where it is used in a lab or the field

Software	OpenChoice	FlukeView®	FlukeView® makes it easy to extract, analyze and document waveforms
Probe size	Lab size	Industrial size	Optional Fluke VPS-510-x Probes offer same size and performance as standard lab grade scope probe

ข้อมูลจำเพาะ: Fluke ScopeMeter 190-204/S Portable Digital Oscilloscope

Specifications	
Bandwidth	200 MHz
Number of channels	200 MHz: 4 channels
Real-time sample rate	2.5 GS/s
Inputs	4 scope plus DMM input
Independently floating isolated inputs	Up to 1000 V CAT III/600 V CAT IV between inputs, references and ground
Timebase range	2 ns - 2 min/div
Input sensitivity	2 mV-100 V/div
Trigger types	Connect-and-View™, Free Run, Single Shot, Edge, Delay, Dual Slope, Video, Video Line, Selectable pulse width, N-Cycle
Trigger source	Any scope input channel
Glitch capture	8 ns
Scope measurements	Cursor: 7
	Automatic: 30
Maximum record length	ScopeRecord mode: 30,000 pts
	Scope mode: 10,000 pts per input
Persistence	Digital persistence giving analog oscilloscope-like waveform decay
Waveform compare	Waveform reference with automatic Pass/Fail testing
Environmental Specifications	
Operating temperature	0 °C to 40 °C Including Batteries
	0 °C to 50 °C Excluding Batteries
Storage temperature	-20 °C to +60 °C
Operating altitude	Up to 2,000 m (6666 ft) for CAT IV 600 V, CAT III 1000 V
	Up to 3,000 m (10,000 ft) for CAT III 600 V, CAT II 1000 V
Safety Specifications	
Electrical safety	1,000 V CAT III/600V CAT IV (EN61010-1)
Mechanical and General Specifications	
Size	270 x 190 x 70 mm
Weight	2.2 kg



Warranty	3-years on main instrument, 1-year on accessories
Li-Ion Battery	BP291 4800 mAh battery up to 7 hours included standard
Included Accessories	
	VPS410 Voltage Probe Sets (one red, one blue, one grey, one green)
	BC190 Battery Charger/mains Adapter
	BP291 4800 mAh high capacity Li-ion Battery
	Handstrap (affixed to instrument)
	Hangstrap
	Multi-Language User Manuals on CD-Rom
	FlukeView ScopeMeter® demo package (restricted functionality)
	USB Interface Cable
Warranty	Three years on main instrument, one year on accessories

รุ่น



Fluke 190-204/S

Fluke 190-204/S ScopeMeter® Test Tool

Includes:

- Color ScopeMeter® 200 MHz
- 4 channels
- DMM/Ext.input
- C290 Hard-shell Carrying Case
- SW90W FlukeView for ScopeMeter Test Tool
- Windows® software

Fluke. ให้โลกของคุณ คงอยู่แต่ละก้าวต่อไป

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa
+31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com/th-th

©2021 Fluke Corporation. Specifications subject to
change without notice.
12/2021

Modification of this document is not permitted without
written permission from Fluke Corporation.