

Teknik veriler

LVD2 Volt Işıđı

Temel özellikler

- Çift hassasiyet
- 100,000 saat ömürlü LED ışığı
- 90 ile 600 V AC arasını algılar
- CAT IV 600 V sınıfı
- Çift Algılama Seviyesi
- Mavi renk AC Voltaj kaynağına yakın olduğunu gösterir
- Kırmızı ise kaynakta olduğunuzu gösterir
- 0 derece C ile 50 derece C arası çalışma sıcaklığı
- Ultra Parlak Beyaz LED
- 100,000 saat ömür
- AAA pil dahildir.

Ürün İncelemesi: LVD2 Volt Işıđı

Temassız AC voltaj dedektörü ve LED el lambası tek bir kullanışlı, kompakt tasarımda. LVD2, ticari ve endüstriyel uygulamalar için uygun bir CAT IV 600 V sınıfı temassız dedektördür. LVD2'de, kaynaktan 1" ile 5" (2.54 cm ile 12.7 cm arası) arası uzakta iken mavi renk olan ve kaynakta iken kırmızı renk olan çift hassasiyet özelliđi bulunur.

Fluke. *Keeping your world up and running.®*

Fluke TURKIYE
P.O. Box 1186
5602 BD Eindhoven
The Netherlands
www.fluke.com.tr

©2022 Fluke Corporation. All rights reserved.
Data subject to alteration without notice.
01/2022

Mer information:

U.S.A. (800) 443-5853 TR +31 (0)40 267 5100 Canada
(905) 890-7600 Övrigt +1 (425) 446-5500

**Modification of this document is not permitted
without written permission from Fluke Corporation.**