

Teknik veriler

Fluke 373 True-rms AC Clamp Meter



Temel özellikler

- 600 A ac current measurement with fixed jaw
- 600 V ac and dc voltage measurement
- State of the art signal processing allows for use in noisy electrical environments while providing stable readings
- CAT IV 300 V, CAT III 600 V
- True-rms ac voltage and current for accurate measurements on non-linear signals
- Large, easy to read backlight display automatically sets the correct measurement range so you do not need to change the switch positions while taking a measurement
- Three-year warranty
- Soft carrying case

Ürün İncelemesi: Fluke 373 True-rms AC Clamp Meter

Be ready for anything.





The new Fluke 373 Clamp Meter offers improved performance perfect for any ac only current measurement situations. Featuring true-rms ac voltage and current measurements, and resistance measurement up to 6000Ω with continuity detection, the Fluke 373 is everything you need, plus a little more.

Safety Conformance

EN/IEC 61010-1:2001; 600V CAT III, 300V CAT IV

Özellikler: Fluke 373 True-rms AC Clamp Meter

Elektrik Teknik Özellikleri	
AC Akımı	
Aralık	600,0 A
Çözünürlük	0,1 A
Hassaslık	%2 + 5 basamak (48 - 62 Hz)
Crest Faktörü (50/60 Hz)	2,5 @ 600 A
AC Gerilimi	
Aralık	600,0 V
Çözünürlük	0,1 V
Hassaslık	%1,0 + 5 basamak (48 - 62 Hz)
DC Voltaj	
Aralık	600,0 V
Çözünürlük	0,1 V
Hassaslık	%1 ± 5 basamak
Direnç	
Aralık	600,0 Ω/6000 Ω
Çözünürlük	0,1 Ω/1 Ω
Hassaslık	%1 ± 5 basamak
Devamlılık Sesli Uyarı Cihazı	30 Ω
Kapasitans	
Aralık	10,0 - 100,0 µF / 1000 µF
Çözünürlük	0,1 µF/1 µF
Hassaslık	% 1,9 ± 2 basamak
Mekanik Özellikler	
Boyut (U x G x Y)	232 mm x 85 mm x 45 mm
Ağırlık	370 g
Ortam Özellikleri	
Çalışma Sıcaklığı	-10°C - +50°C
Saklama Sıcaklığı	-40°C - +60°C
Çalışma Nemi	Yoğuşmasız (< 10°C) ≤ %90 RH (10°C ila 30°C'de) ≤ %75 RH (30°C ila 40°C'de) ≤ %45 RH (40°C ila 50°C'de) (Yoğuşma olmadan)
Çalışma Yüksekliği	3000 metre
Depolama Yüksekliği	12.000 metre
EMI, EMC	Yürürlükteki tüm EN61326-1:2006 gereksinimlerini karşılar

Sıcaklık Katsayıları	28°C üzerindeki veya 18°C altındaki her bir °C için 0,1 x oranında belirtilen hassasiyet ekleyin
Güvenlik Uyumluluğu	ANSI/ISA S82.02.01:2004 CAN/CSA-C22.2 No. 61010-1-04 IEC/EN 61010-1:2001, 600V CAT III, 300V CAT IV Kirlilik Derecesi 2 EN/IEC 61010-2-32:2002 EN/IEC 61010-031:2002/A1:2008 
Kurum Onayları	  
Piller	2 AA, NEDA 15A, IEC LR6

Modeller



Fluke 373

True-rms AC Clamp Meter

Included accessories:

- Coated instruction card
- Safety information sheet
- Soft carrying case
- TL75 test leads
- Five AA Alkaline batteries

Fluke. *Keeping your world up and running.®*

Fluke TURKIYE
P.O. Box 1186
5602 BD Eindhoven
The Netherlands
www.fluke.com.tr

©2022 Fluke Corporation. All rights reserved.
Data subject to alteration without notice.
01/2022

Mer information:

U.S.A. (800) 443-5853 TR +31 (0)40 267 5100 Canada
(905) 890-7600 Övrigt +1 (425) 446-5500

**Modification of this document is not permitted
without written permission from Fluke Corporation.**