

Thông số kỹ thuật

## Fluke PM9091/001 50 Ohm Coaxial BNC cable set (3 x 1.5m)




### Tính năng chính

- Cable length is 1.5 m
- Maximum Signal Voltage: 300 V rms
- Maximum Voltage to Ground: 600 V rms. CAT III per IEC 61010-031
- BB120 Shielded Banana to BNC Adapter is required to adapt to ScopeMeter 120 Series shielded banana jack inputs

### Tổng quan sản phẩm: Fluke PM9091/001 50 Ohm Coaxial BNC cable set (3 x 1.5m)

Each set consists of three black cables with colored BNC male connectors (red, gray and black) for easy identification.

## Model



### **Fluke PM9091**

50 Ohm Coaxial BNC cable set (3 x 1.5m)

---

**Fluke.** *Giữ cho thế giới của bạn. không ngừng vận động.*

**Fluke Corporation**

PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

**Representative office of Fluke South East Asia Pte Ltd**

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: [info.asean@fluke.com](mailto:info.asean@fluke.com)

[www.fluke.com/vn](http://www.fluke.com/vn)

©2022 Fluke Corporation. Specifications subject to change without notice.

01/2022

**Modification of this document is not permitted without written permission from Fluke Corporation.**