

Thông số kỹ thuật

## Cáp nối Fluke I17XX-FLEX2M-M2M1P



### Tổng quan sản phẩm: Cáp nối Fluke I17XX-FLEX2M-M2M1P

Cáp nối đực-đực, dài 2 mét để nối các máy ghi điện Fluke 1730 và 1740 series với Cửa đo điện Fluke PQ400.

## Model



### **Fluke I17XX-FLEX2M-M2M1P**

Fluke I17XX-FLEX2M-M2M1P

- Cáp nối đực-đực dài 2 mét (1 cáp)

**Fluke.** *Giữ cho thế giới của bạn. không ngừng vận động.*

**Fluke Corporation**

PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

**Representative office of Fluke South East Asia Pte Ltd**

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: info.asean@fluke.com

www.fluke.com/vn

©2022 Fluke Corporation. Specifications subject to change without notice.

01/2022

**Modification of this document is not permitted without written permission from Fluke Corporation.**