

Thông số kỹ thuật

Fluke BP7235 NiMH Battery Pack

Tính năng chính

7.2V 3500 mA-hour rechargeable Ni-MH battery pack. This item replaces BP7217 Ni-Cd Battery Pack

Includes one battery pack.

Tổng quan sản phẩm: Fluke BP7235 NiMH Battery Pack

Description: 7.2V 3500 mA-hour rechargeable Ni-MH battery pack.

Application: Provides typical 16-hour battery life when used in 700 or 740 Calibrator.

Included: One battery pack.

Material: Six 1.2V dc Ni-MH cells in custom-molded ABS/PC-blend case.

Application: 7.1" x 2.2" x .9" (150 mm x 56 mm x 22 mm)

Dimensions: 7.1" x 2.2" x .9" (150 mm x 56 mm x 22 mm)

Weight: 11 oz/310g

Warranty: One year

Thông số kỹ thuật: Fluke BP7235 NiMH Battery Pack

General Specifications	
Material	Six 1.2 V DC Ni-MH cells in custom-molded ABS/PC-blend case
Application	7.1 x 2.2 x .9 in (150 x 56 x 22 mm)
Dimensions	7.1 x 2.2 x .9 in (150 x 56 x 22 mm)
Weight	11 oz / 310g
Warranty	One year
This item replaces BP7217 Ni-Cd Battery Pack.	

Model

Fluke BP7235

NiMH Battery Pack

Fluke. *Giữ cho thế giới của bạn. không ngừng vận động.*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

Representative office of Fluke South East Asia Pte Ltd

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: info.asean@fluke.com

www.fluke.com/vn

©2022 Fluke Corporation. Specifications subject to change without notice.

01/2022

Modification of this document is not permitted without written permission from Fluke Corporation.