

Thông số kỹ thuật

Fluke CXT80 Extreme Case



Tính năng chính

- Buoyancy allows case to float in salt water with 3.6 kg (7.94 lb) load
- Includes an automatic purge valve for quick equalization after changes in atmospheric pressure
- Features an exclusive 6.4 mm (0.25 in) neoprene O-ring and ABS latches for excellent seal

Tổng quan sản phẩm: Fluke CXT80 Extreme Case

Unbreakable, watertight, airtight, dustproof, chemical resistant and corrosion proof.

Model



Fluke CXT80

For use with the following test tools:

- Multimeters: 27, 83 V, 85 V, 87 V, 187, 189
 - Process Tools: 724, 725, 726, 789
-

Fluke. *Giữ cho thế giới của bạn. không ngừng vận động.*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

Representative office of Fluke South East Asia Pte Ltd

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: info.asean@fluke.com

www.fluke.com/vn

©2022 Fluke Corporation. Specifications subject to change without notice.

01/2022

Modification of this document is not permitted without written permission from Fluke Corporation.