

Thông số kỹ thuật


Fluke 3210-PR-TF 1000A Flex Thin Flex Current Probe (24 inch/60cm)



Tổng quan sản phẩm: Fluke 3210-PR-TF 1000A Flex Thin Flex Current Probe (24 inch/60cm)

The Fluke 3210-PR-TF 1000A Flex Thin Flex Current Probe is an ac current probe utilizing the Rogowski principle. The Fluke 3210PRTF Probe is designed for use with the Fluke 1750 Power Recorder and measures current from very low frequencies up to the 50th harmonic of a 50/60 Hz power supply. The flexible and lightweight measuring head allows quick and easy installation in hard to reach areas and around large conductors.

Model



Fluke 3210-PR-TF

1000A Flex Thin Flex Current Probe (24 inch/60cm)

Fluke. *Giữ cho thế giới của bạn. không ngừng vận động.*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

Representative office of Fluke South East Asia Pte Ltd

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: info.asean@fluke.com

www.fluke.com/vn

©2022 Fluke Corporation. Specifications subject to change without notice.

01/2022

Modification of this document is not permitted without written permission from Fluke Corporation.