

Thông số kỹ thuật


Fluke i1730-flex6000 iFlex® Current Clamp



Tổng quan sản phẩm: Fluke i1730-flex6000 iFlex® Current Clamp

Đầu dò dòng 36 inch iFlex của thiết bị ghi thông số điện năng Fluke 1730 giúp mở rộng dải đo của thiết bị Fluke 1730 lên đến 6000A AC trong khi vẫn cung cấp độ linh hoạt tối ưu cho việc đo lường. Đầu dò iFlex nối trực tiếp với thiết bị ghi thông số điện năng, hiển thị các thông số dòng đo được mà không cần các hệ số tỷ lệ khả năng gây lỗi. Dây nối dài 1,8 m (6 ft) giúp có thể đứng xa điểm đo và nhìn màn hình hiển thị trên thiết bị ghi dễ hơn. Có các loại dây cáp cho thiết bị Fluke 1730 iFlex 12, 24 và 36 inch

Model



Fluke i1730-flex6000

A 36 inch Current Clamp

Fluke. *Giữ cho thế giới của bạn. không ngừng vận động.*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

Representative office of Fluke South East Asia Pte Ltd

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: info.asean@fluke.com

www.fluke.com/vn

©2022 Fluke Corporation. Specifications subject to change without notice.

01/2022

Modification of this document is not permitted without written permission from Fluke Corporation.