

Thông số kỹ thuật

## Kìm đo dòng Fluke i17XX-flex1500/4pk iFlex®



### Tổng quan sản phẩm: Kìm đo dòng Fluke i17XX-flex1500/4pk iFlex®

Đầu dò dòng linh hoạt 12 inch iFlex của Fluke 17XX giúp mở rộng dải đo của Thiết bị ghi thông số điện năng hoặc năng lượng Fluke 17XX lên đến 1500 A ac trong khi vẫn cung cấp độ linh hoạt tối ưu cho việc đo lường. Đầu dò iFlex nối trực tiếp với thiết bị ghi thông số điện năng, hiển thị các thông số dòng đo được mà không cần các hệ số tỷ lệ có khả năng gây lỗi. Dây nối dài 1,8 m (6 ft) giúp có thể đứng xa điểm đo và nhìn màn hình hiển thị trên thiết bị ghi dễ hơn. Các loại dây cáp cho thiết bị Fluke 17XX iFlex có sẵn là 12, 24 và 36 inch.

## Model



### **i17XX-flex1500/4pk**

1500A 12 inch, 4 pack iFlex® Current Clamps

---

**Fluke.** *Giữ cho thế giới của bạn. không ngừng vận động.*

**Fluke Corporation**

PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

**Representative office of Fluke South East Asia Pte Ltd**

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: info.asean@fluke.com

www.fluke.com/vn

©2022 Fluke Corporation. Specifications subject to change without notice.

01/2022

**Modification of this document is not permitted without written permission from Fluke Corporation.**