


Thông số kỹ thuật

Fluke i430 Flex Current Clamp



Tổng quan sản phẩm: Fluke i430 Flex Current Clamp

The i430 Flex is an AC current probe utilizing the Rogowski principle. The flexible and lightweight measuring head allows quick and easy installation in hard to reach areas, without batteries or an external power source.

Also available as a pack of 4 pieces of the i430 current clamp, to be used for high current measurements. The Flex clamp fits around bus bars and large or hard-to-reach conductors. This 4-pack is perfect for use with 3-phase tools such as the Fluke 430 series.

Thông số kỹ thuật: Fluke i430 Flex Current Clamp

General Specifications	
Probe and Cable Material	TPE rubber, reinforced insulation
	UL94 V-0, Colour: RED Munsell 7.5
	R 1/14
Couplings Material	Polypropylene, UL94 V-0
Probe Cable Length	610 mm

Probe Cable Diameter	12.4 mm
Probe Cable Bend Radius	40 mm
Output cable length	2.5 meters RG58
Output Connector	Safety BNC Connector
Operating Range	-20 to +90°C
Storage Temperature	-40 to +105°C
Operating Humidity	15% to 85% (non condensing)
Degree of protection (Probe)	IP41
Specifications	
Current Range	3000 A AC RMS
Voltage output (@1000 ARMS, 50 Hz)	85 mV
Accuracy	± 1% of reading (@ 25°C, 50 Hz)
Linearity (10% to 100% of range)	± 0.2% of reading
Noise (10 Hz - 7 kHz)	1.0 mV ACRMS
Output impedance	82 Ω min
Load Impedance	50 kΩ
Internal Resistance per 100 mm probe length	10.5Ω ± 5%
Bandwidth (-3dB)	10 Hz to 7 kHz
Phase Error (45 - 65 Hz)	±1°
Position Sensitivity	± 2% of reading max.
Temperature Coefficient	± 0.08% max of reading per °C
Working Voltage (see Safety Standards section)	1000 V AC RMS or DC (head) 30 V max. (output)
Safety Specifications	



Safety Standards	BS EN 61010-1 2001
	BS EN 61010-2-032 2002
	BS EN 61010-031 2002, 1000 VRMS, Category III, Pollution Degree 2
	Use of the probe on uninsulated conductors is limited to 1000 V AC RMS or DC and frequencies below 1 kHz.
	Please note that this probe is designed to work with Fluke 435, if used with other products
	safety rating for the output to earth is limited to 600V AC RMS or DC.

Model



Fluke i430

Fluke. *Giữ cho thế giới của bạn. không ngừng vận động.*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

Representative office of Fluke South East Asia Pte Ltd

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: info.asean@fluke.com

www.fluke.com/vn

©2022 Fluke Corporation. Specifications subject to change without notice.

01/2022

Modification of this document is not permitted without written permission from Fluke Corporation.