


Thông số kỹ thuật

Cụm cầu chì Fluke 440 mA



Tính năng chính

- Thiết kế cho đồng hồ đo vạn năng an toàn cháy nổ Fluke 28 II Ex
- Thiết kế ngăn kích nổ trong môi trường khí dễ cháy
- Một phần của thiết kế sản phẩm an toàn cháy nổ

Tổng quan sản phẩm: Cụm cầu chì Fluke 440 mA

Model	P/N 203403 11A 1000 V	P/N 203411 440 mA 1000V	P/N 2279229 315 mA 1000V	Cụm cầu chì P/N 4016494 440 mA
107, 115, 117, 233	●			
175, 177, 179, 83V 87V, 287, 289. 27II, 28II, 88V, 77IV, 87V MAX	●	●		
3000 FC, 1577, 1587 FC BT508, BT510, BT521		●		
787, 787B, 789		● số lượng 2		
1503, 1507			●	
28II Ex	●			●

Đồng hồ vạn năng kỹ thuật số an toàn cháy nổ Fluke 28II Ex được thiết kế để ngăn sự cố, kích nổ môi trường khí dễ cháy. Sử dụng khối cầu chì thay thế phù hợp là rất cần thiết cho tính năng an toàn của thiết kế trên. Cụm cầu chì Fluke 440 mA được thiết kế đặc biệt để sử dụng cho Fluke 28II.

Được dùng trong Đồng hồ vạn năng kỹ thuật số của Fluke

[Đồng hồ đo vạn năng kỹ thuật số hiệu dụng thực an toàn cháy nổ Fluke 28 II Ex](#)

Fluke. *Giữ cho thế giới của bạn. không ngừng vận động.*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

Representative office of Fluke South East Asia Pte Ltd

C/O Danaher Vietnam
Green Power Tower, 11th Floor Unit 2
35 Ton Duch Thang Street, District 1
Ho Chi Minh City
Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: info.asean@fluke.com

www.fluke.com/vn

©2022 Fluke Corporation. Specifications subject to change without notice.

01/2022

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

Modification of this document is not permitted without written permission from Fluke Corporation.