

Thông số kỹ thuật

Fluke L207 High Intensity Light with Collector's Cap

Tính năng chính

- Cap adjusts for all-day comfort
- Light attaches to bill of baseball cap
- Rugged light withstands 6' drops to concrete
- Waterproof light case won't crack or chip
- Electrically and thermally nonconductive

Tổng quan sản phẩm: Fluke L207 High Intensity Light with Collector's Cap

Powerful, lightweight, mini-Xenon worklight shines right where you're working. Comes with limited edition Fluke collector's cap.

Model

Fluke L207

Fluke L207 High Intensity Light with Collector's Cap

Fluke. *Giữ cho thế giới của bạn. không ngừng vận động.*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

Representative office of Fluke South East Asia Pte Ltd

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: info.asean@fluke.com

www.fluke.com/vn

©2022 Fluke Corporation. Specifications subject to change without notice.

01/2022

Modification of this document is not permitted without written permission from Fluke Corporation.