

Thông số kỹ thuật

Fluke 700 PMP Pressure Pump



Tổng quan sản phẩm: Fluke 700 PMP Pressure Pump

Description: The Fluke 700PMP is a hand-operated pressure pump to provide pressures up to 150 psi/1000 kPa. Output fitting is 1/8 FNPT.

Application: Linear stroke of 4 cm. Multi-turn vernier for fine adjustment of pressure.

Thông số kỹ thuật: Fluke 700 PMP Pressure Pump

Mechanical and General Specifications

Size	265 x 35 mm
Weight	340 g
Warranty	One year

Model



Fluke 700PMP

PMP Pressure Pump

Instruction sheet

Fluke. Giữ cho thế giới của bạn. không ngừng vận động.

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

Representative office of Fluke South East Asia Pte Ltd

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: info.asean@fluke.com

www.fluke.com/vn

©2022 Fluke Corporation. Specifications subject to change without notice.

01/2022

Modification of this document is not permitted without written permission from Fluke Corporation.