

Thông số kỹ thuật

## VPS212-R - Voltage Probe Set, 10:1, one red



### Tổng quan sản phẩm: VPS212-R - Voltage Probe Set, 10:1, one red

Double insulated voltage probe for ScopeMeter 190 series.

**Each probe set includes:**

- 600 V CAT III / 1000 V CAT II rated 10:1 Voltage Probe
- Hook Clip for Probe Tip
- Ground Lead with Mini Alligator
- Insulation Sleeve
- 30 V CAT II rated Ground Spring for Probe Tip

**Specification:**

- Attenuation: 10x
- Bandwidth: 200 MHz
- Max. Input Voltage 1000 V CAT II or 600 V CAT III
- Max. Voltage to ground: 1000 V CAT II or 600 V CAT III per IEC / EN61010-031
- Input Resistance: 10 M $\Omega$
- Input Capacitance: 18 pF
- Compensation range: 10 to 30 pF
- Cable Length: 2.5 m

## Thông số kỹ thuật: VPS212-R - Voltage Probe Set, 10:1, one red

Specification	
Attenuation	10x
Bandwidth	200 MHz
Max. input voltage	1000 V CAT II or 600 V CAT III
Max. voltage to ground	1000 V CAT II or 600 V CAT III per IEC / EN61010-031
Input resistance	10 M $\Omega$
Input capacitance	18 pF
Compensation range	10 to 30 pF
Cable length	2.5 m

**Fluke.** *Giữ cho thế giới của bạn. không ngừng vận động.*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**Representative office of Fluke South East Asia Pte Ltd**

C/O Danaher Vietnam  
Green Power Tower, 11th Floor Unit 2  
35 Ton Duch Thang Street, District 1  
Ho Chi Minh City  
Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: [info.asean@fluke.com](mailto:info.asean@fluke.com)

[www.fluke.com/vn](http://www.fluke.com/vn)

©2022 Fluke Corporation. Specifications subject to change without notice.  
01/2022

**For more information call:**

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

**Modification of this document is not permitted without written permission from Fluke Corporation.**