

Thông số kỹ thuật

Máy nội soi công nghiệp Fluke 9 MM với tang quấn đầu dò 20 M



Tính năng chính

Đầu dò máy nội soi công nghiệp 9 milimet, tang quấn 20 mét tùy chọn có camera mặt trước. Tương thích với máy nội soi công nghiệp Fluke DS701 và Fluke DS703 FC. Hỗ trợ tất cả các tính năng của máy nội soi công nghiệp Fluke, ngoại trừ công nghệ Up is Up™

Tổng quan sản phẩm: Máy nội soi công nghiệp Fluke 9 MM với tang quấn đầu dò 20 M

Ống nước

- Kiểm tra tắc nghẽn và rác thải trong đường ống
- Kiểm tra thiết bị phun nước

HVAC

- Kiểm tra đường ống

Fluke. Giữ cho thế giới của bạn. không ngừng vận động.

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

Representative office of Fluke South East Asia Pte Ltd

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: info.asean@fluke.com

www.fluke.com/vn

©2022 Fluke Corporation. Specifications subject to change without notice.

01/2022

Modification of this document is not permitted without written permission from Fluke Corporation.