

Thông số kỹ thuật

Phụ kiện gắn chân máy Fluke 3

Tổng quan sản phẩm: Phụ kiện gắn chân máy Fluke 3

Phụ kiện gắn chân máy liền khối được thiết kế đặc biệt cho phép gắn Camera Hồng ngoại Ti400, Ti300 hoặc Ti200 nhanh chóng và dễ dàng vào chân máy một hoặc ba chân tiêu chuẩn để dùng cho các ứng dụng hoặc tình huống đòi hỏi phải có nền ổn định hơn hoặc bán cố định.

Model

Fluke TriPod 3

Tripod Mounting Base

p>Use with Ti400, Ti300 and Ti200 Infrared Cameras.

Fluke. *Giữ cho thế giới của bạn. không ngừng vận động.*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

Representative office of Fluke South East Asia Pte Ltd

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: info.asean@fluke.com

www.fluke.com/vn

©2022 Fluke Corporation. Specifications subject to change without notice.

01/2022

Modification of this document is not permitted without written permission from Fluke Corporation.