

Thông số kỹ thuật

## Fluke 700PCK Pressure Calibration Kit



### Tổng quan sản phẩm: Fluke 700PCK Pressure Calibration Kit

**Description:** The Fluke 700PCK makes it possible to calibrate your pressure modules at your facility using your own precision pressure standards.

**Application:** When installed on your PC, the WindowsT-based software easily steps you through an as-found verification, a calibration adjustment, and an as-left verification. Calibration data is captured for import to your database. A 386 or better PC running Windows 3.1 or better is required, along with a precision pressure standard with an uncertainty of less than 1/4 that of the pressure module being verified.

## Model



### **Fluke 700PCK**

Pressure Calibration Kit

---

Included: The kit consists of a power supply, an interface adapter, appropriate cables, and Fluke 700PC Pressure Module Calibration Software.

Warranty: One year

---

**Fluke.** *Giữ cho thế giới của bạn. không ngừng vận động.*

**Fluke Corporation**

PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

**Representative office of Fluke South East Asia Pte Ltd**

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: [info.asean@fluke.com](mailto:info.asean@fluke.com)

[www.fluke.com/vn](http://www.fluke.com/vn)

©2021 Fluke Corporation. Specifications subject to change without notice.

10/2021

**Modification of this document is not permitted without written permission from Fluke Corporation.**