

Thông số kỹ thuật

# Fluke Networks CIQ-KRQ Copper Qualification Tester Kit



## Tính năng chính

- Troubleshoots copper cabling and qualifies for 10/100/Gig Ethernet
- CableIQ™ qualification tester with adapters and patch cords
- Graphically maps wiring configuration and shows distance to fault
- Quickly verifies network drops: link & ping functionality
- Supports copper media cabling: twisted-pair, coax, audio

## Tổng quan sản phẩm: Fluke Networks CIQ-KRQ Copper Qualification Tester Kit

The CableIQ™ Residential Qualifier Kit for copper cabling installers troubleshoots and qualifies Ethernet network cabling speeds on active networks. Includes patch cords and multiple adapter types for network technicians to quickly solve connectivity problems.

## Thông số kỹ thuật: Fluke Networks CIQ-KRQ Copper Qualification Tester Kit

Cable types supported	UTP, STP, FTP, SSTP, RG6, RG59, audio and security
Qualification autotests	1000BASE-T, 100BASE-TX, 10BASE-T, VoIP, 1394b S100, TELCO, Wiremap only, Coax
Supported tests	Wiremap, length, cable signal performance, digital toner, analog toner, Ethernet port detection and identification, analog telephone detection, blink port light, continuity, speaker test, cable fault finding, video signal detection.
Wiremap	Can detect single wire faults and supports MultiMap mode with up to seven remote office identifiers. Draws proportional wire length to breaks. Detects split pairs.
Find fault	Measures crosstalk and impedance and compares against appropriate limits based on qualification test selected. Detects location of large point sources as well as distributed sources in the cabling if they are sufficient to disqualify the application
Results storage	Up to 250 qualification test results
Power	Battery type: 4 AA (NEDA 15A, IEC LR6) alkaline batteries
Battery life	20 hours of typical use, without backlight
Other battery types supported	4AA photo lithium, NIHM, NICAD
Dimensions and weight	7in x 3.5in x 1.75in (17.8cm x 8.9cm x 4.5cm) 1.2 lb (0.55 kg)

**Fluke.** *Giữ cho thế giới của bạn. không ngừng vận động.*

**Fluke Corporation**

PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

**Representative office of Fluke South East Asia Pte Ltd**

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: [info.asean@fluke.com](mailto:info.asean@fluke.com)

[www.fluke.com/vn](http://www.fluke.com/vn)

©2022 Fluke Corporation. Specifications subject to change without notice.

01/2022

**Modification of this document is not permitted without written permission from Fluke Corporation.**