

Thông số kỹ thuật

Fluke 62 MAX+/323/1AC IR Thermometer, Clamp Meter and Voltage Detector Kit



Tính năng chính

Fluke 62 MAX+. Small in size. Big on toughness.

- Dust and water-resistant: IP54 rated.
- Rugged: 3-meter (9.8-foot) drop tested.
- Ergonomically designed: Completely redesigned for a more natural hand fit.
- Distance to spot: 12:1.
- Dual lasers: Identifies area to be measured.
- Large, backlit display: Makes data easier to read, even in dark areas.

Fluke 323 True-rms Clamp Meter. Rugged. Reliable. Precise.

- 400 A AC current measurement.
- 600 VAC and DC voltage measurement.
- True RMS AC voltage and current for accurate measurements on non-linear signals.
- Resistance measurement up to 40 kΩ with continuity detection.
- Slim, ergonomic design.
- CAT IV 300V/CAT III 600 V safety rating.

Fluke 1AC II VoltAlert™ Voltage Detector

- Voltbeat™ technology and continuous self-test, so always know it's working.
- Upon detection, tip glows and beeper sounds.
- Voltage detection of 90 to 1000 VAC.
- CAT IV 1000 V for added protection.

Fluke C115 Soft Case

- Lightweight soft case to provide optimal protection and accessory storage.

Tổng quan sản phẩm: Fluke 62 MAX+/323/1AC IR Thermometer, Clamp Meter and Voltage Detector Kit

This kit is designed to help electricians and HVAC technicians solve problems quicker. Test first for overheated electrical devices using an IR thermometer; then use the clamp meter and voltage detector to find out more about the problem

Thông số kỹ thuật: Fluke 62 MAX+/323/1AC IR Thermometer, Clamp Meter and Voltage Detector Kit

Fluke 62 MAX+ Infrared Thermometer

Specifications		
Temperature range	-30°C to 650°C (-22°F to 1202°F)	
Accuracy	±1.0°C or ±1.0% of reading, whichever is greater -10°C to 0°C: ±2.0 -30°C to -10°C: ±3.0	
Response time (95%)	< 300 ms (95% of reading)	
	Spectral response	8 to 14 microns
	Emissivity	0.10 to 1.00
Optical resolution	12:1 (calculated at 90% energy)	
Display resolution	0.1°C (0.2°F)	
Repeatability of readings	±0.5% of reading or < ±0.5°C (1°F), whichever is greater	
Power	AA battery	
Battery life	8 hours with laser and backlight on	
Physical Specifications		
Weight	255 g (8.99 oz)	
Size	175 x 85 x 75 mm (6.88 x 3.34 x 2.95 in)	

Operating temperature	0°C to 50°C (32°F to 122°F)	
Storage temperature	-20°C to 60°C (-4°F to 140°F), (without battery)	
Operating humidity	10% to 90% RH non-condensing at 30°C (86°F)	
Operating altitude	2000 meters above mean sea level	
Storage altitude	12,000 meters above mean sea level	
IP rating	IP 54 per IEC 60529	
Drop test	3 meters	
Vibration and shock	IEC 68-2-6 2.5 g, 10 to 200 Hz, IEC 68-2-27, 50 g, 11 ms	
EMC	EN 61326-1:2006 EN 61326-2:2006	
Standards and agency approval	Compliance	EN/IEC 61010-1: 2001
	Laser safety	FDA and EN 60825-1 Class II

Fluke 323 True RMS Clamp Meter

Specifications		
AC current	Range	400.0 A
	Accuracy	2% ±5 digits (45 Hz to 65 Hz) 2.5% ±5 digits (65 Hz to 400 Hz)
AC voltage	Range	600.0 V
	Accuracy	1.5% ±5 digits
DC voltage	Range	600.0 V
	Accuracy	1.0% ±5 digits
Resistance	Range	400.0 Ω/ 4000 Ω
	Accuracy	1.0% ±5 digits
Continuity		≤ 70 Ω
AC response		True-rms
Data hold		Yes
Size	H x W x D (mm)	207 x 75 x 34
	Max wire diameter	30 mm (600 MCM)
	Weight	265 g
Category rating		CAT III 600 V CAT IV 300 V
Warranty		Two-year

Fluke 1AC-II VoltAlert

Specifications	
Operating principle	Senses the steady state electrostatic field produced by ac voltage through insulation without requiring contact to the bare conductor. A red glow at the tip and a beeping noise (if not switched OFF) indicates the presence of voltage.
Voltage sensing ranges	Nominally, 90 VAC to 1000 VAC or 200 VAC to 1000 VAC depending on model, 45 Hz to 405 Hz; also a 20 V to 90 V control circuit model
Detector tip style	Blade or round, depending on model
Light source	One high intensity red LED
Agency approvals	c CSA us, CE, C-Tick
Safety rating	1000 V, CAT IV
IP rating	IP 40
Operating temperature	-10°C to 50°C
Operating humidity ranges	0% to 95% (0°C to 30°C)
	0% to 75% (30°C to 40°C)
	0% to 45% (40°C to 55°C)
Operating altitude	3000 meters
Batteries	2 AAA alkaline batteries included
Product does not respond to random electrostatic discharge.	

Model



Fluke 62 MAX+/323/1AC Kit

Fluke 62 MAX+/323/1AC IR Thermometer, Clamp Meter and Voltage Detector Kit

Includes:

- Fluke 62 MAX+ IR Thermometer
 - Fluke 323 True-rms Clamp Meter
 - Fluke 1AC II VoltAlert Voltage Detector
 - C115 Soft Case
-

Fluke. *Giữ cho thế giới của bạn. không ngừng vận động.*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

Representative office of Fluke South East Asia Pte Ltd

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: info.asean@fluke.com

www.fluke.com/vn

©2022 Fluke Corporation. Specifications subject to change without notice.

01/2022

Modification of this document is not permitted without written permission from Fluke Corporation.