

TL71 Premium 測試導線組



主要功能

- 一對（紅，黑）握感舒適探棒用矽膠絕緣，直角式測試導線。
- 推薦用 μV 量測。
- CAT II 1000 V、10 A rating 等級。
- CAT III 1000 V、CAT IV 600V 只用防護帽。
- 一年保固。

產品概述: TL71 Premium 測試導線組

The Fluke TL71 Premium Multimeter Test Lead Set is a pair of comfort grip probes (red and black) with flexible silicone-insulated, right-angle test leads. These distinctive comfort grip probes are heat and cold resistant.

As with all Fluke products, these test leads undergo a battery of safety tests to be rated at:

CAT II 1000 V, 10 A rating

CAT III 1000 V, CAT IV 600V with protective cap

The WearGuard™ test lead indicator shows wear and tear easier. It exposes a contrasting color when the leads are damaged and need to be replaced. Silicone-insulated leads have superior flexibility in cold temperatures and resistance to high temperatures.

The Fluke TL71 Premium Test Leads are compatible with all instruments that accept standard 4 mm (0.16 in) shrouded banana connectors. Some of the compatible tools include:

Fluke 902 FC True-RMS HVAC Clamp Meter

Fluke 87V Industrial Multimeter

Fluke 115 Field Technicians Digital Multimeter

Fluke 787B ProcessMeter™

These test leads come with a one-year warranty.

規格: TL71 Premium 測試導線組

Lead Length	1.2 (4 ft), 2mm diameter probe tip
Category Rating	CAT II 1000 V, CAT III 1000 V, CAT IV 600 V, 10 A max
Operating temperature	-20°C to 55°C (-4°F to 131°F), 90 % RH altitude: 2000 m (6,562 ft)

機型

Fluke TL71

Fluke. 保持您的世界運作不懈。

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

更多資訊
U.S.A. (800) 443-5853
Europe/M-East/Africa
+31 (0)40 267 5100
Canada (800)-36-FLUKE
其他 +1 (425) 446-5500
www.fluke.com/zh-tw

©2022 Fluke Corporation. Specifications subject to
change without notice.
01/2022

Modification of this document is not permitted
without written permission from Fluke Corporation.