

Fluke 324 True RMS Clamp Meter



主要功能

測量功能

- 400 A 交流電流測量
- 600 V 交流與直流電壓測量
- 真均方根交流電壓和電流，可準確地測量非線性訊號
- 具連續性偵測的電阻測量，最高可達 4 kΩ
- 溫度與電容測量

特色

- 纖巧的人體工學設計
- 大型、易於讀取的背光顯示幕
- CAT IV 300V/CAT III 600 V 安全等級
- 保留按鍵
- 兩年售後保固
- 軟質攜帶包

產品概述: Fluke 324 True RMS Clamp Meter

Fluke 的堅固耐用。Fluke 的可靠確實。Fluke 的精確無誤。

320 系列電流鉤錶具備真均方根測量與最佳化人體工學設計，因此對商業與住家電氣技師而言，不啻為最理想的一般疑難排除工具。323、324 與 325 經過精心設計，能確認負載電流、交流電壓是否存在，並可確認電路、開關、保險絲與接觸點的連續性。在狹小纜線室中，這些堅固耐用的小型電流鉤錶是測量最高達 400 A 電流的理想選擇。Fluke 324 機型也包括了溫度與電容測量的功能。

規格: Fluke 324 True RMS Clamp Meter

規格		323	324	325
交流電流	範圍	400.0 A	40.00 A/400.0 A	40.00 A/400.0 A
	準確度	2 % ± 5 位數 (45 Hz 至 65 Hz) 2.5 % ± 5 位數 (65 Hz 至 400 Hz)	2 % ± 5 位數 (45 Hz 至 65 Hz) 2.5 % ± 5 位數 (65 Hz 至 400 Hz)	2 % ± 5 位數 (45 Hz 至 65 Hz) 2.5 % ± 5 位數 (65 Hz 至 400 Hz)
直流電流	範圍	-	-	40.00 A/400.0 A
	準確度	-	-	2 % ± 5 位數
交流電壓	範圍	600.0 V	600.0 V	600.0 V
	準確度	1.5 % ± 5 位數	1.5 % ± 5 位數	1.5 % ± 5 位數
直流電壓	範圍	600.0 V	600.0 V	600.0 V
	準確度	1.0 % ± 5 位數	1.0 % ± 5 位數	1.0 % ± 5 位數
電阻	範圍	400.0 Ω / 4000 Ω	400.0 Ω / 4000 Ω	400.0 Ω / 4000 Ω / 40.00 kΩ
	準確度	1.0 % ± 5 位數	1.0 % ± 5 位數	1.0 % ± 5 位數

導通性		≤ 70 Ω	≤ 30 Ω	≤ 30 Ω
電容		-	0 到 100.0 μF / 100 μF 到 1000 μF	0 到 100.0 μF / 100 μF 到 1000 μF
頻率		-	-	5.0 Hz 到 500.0 Hz
交流響應		真均方根值	真均方根值	真均方根值
背光		-	有	有
數據保留		有	有	有
接觸式溫度量測		-	-10.0 °C 至 +400.0 °C (14.0 °F 至 752.0 °F)	-10.0 °C 至 +400.0 °C (14.0 °F 至 752.0 °F)
最小值/最大值		-	-	有
尺寸	高 x 寬 x 深 (mm)	207 x 75 x 34	207 x 75 x 34	207 x 75 x 34
	最大線徑直徑	30 mm (600 MCM)	30 mm (600 MCM)	30 mm (600 MCM)
	重量	265 g	208 g	283 g
分類等級		CAT III 600 V CAT IV 300 V	CAT III 600 V CAT IV 300 V	CAT III 600 V CAT IV 300 V
售後保固		兩年	兩年	兩年

機型

Fluke 324 True-rms Clamp Meter

324 真均方根電流鉤錶

內附配件

- 測試導線
- 軟質包
- 使用手冊

Optional accessories	Description
TL75 Hard Point™ 測試線組	一對（紅、黑）的握感舒適探棒。
Fluke TL175 可旋轉表筆	獲得專利的TwistGuard™擴展的頂罩滿足電氣安全要求最高大多數測量提供了所需的通用性同時減少尖端暴露。
TLK-225 SureGrip™ Master 附件組	Includes all the SureGrip™ leads and probes in a handy six-pocket, roll-up pouch, along with TL224 test leads.

Fluke. 保持您的世界運作不懈。

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

更多資訊
U.S.A. (800) 443-5853
Europe/M-East/Africa
+31 (0)40 267 5100
Canada (800)-36-FLUKE
其他 +1 (425) 446-5500
www.fluke.com/zh-tw

©2022 Fluke Corporation. Specifications subject to
change without notice.
01/2022

Modification of this document is not permitted
without written permission from Fluke Corporation.